BG600-S Series

CHONRY 创锐



- Can automatically save the control parameters when the last power failure
- · For quick cleaning, filling, emptying of pipes
- · After setting the target flow, input the actual flow value, and the system will automatically perform flow correction
- · Pump can be customized to reverse operation after shutdown to prevent liquid dripping
- Support RS485/MODBUS communication protocol, the protocol can also be customized according to customer needs
- Bidirectional high torque, low power consumption motor, can cascade multiple pump heads


Typical Application: Used for admixture conveyors, tubular centrifuges and other equipment.


Max Flow: 12000mL/min

Max speed: 600rpm

Pump head	Model	Hose	ID(mm)	Wall thickness (mm)	Max flow (mL/min)	Max speed (rpm)
A CONTRACTOR OF THE PARTY OF TH	YZ35	73#	9.6	3.3	7400	- 600
		82#	12.7	3.3	12000	
\$11 may	YZ35-13	73#	9.6	3.3	7400	
		82#	12.7	3.3	12000	

Note: The test environment for flow data is normal temperature and pressure, and the test fluid is water. The values are for reference only, please refer to the actual situation.





(Unit: mm)